

Choose the frame and seat combination to find the max. load



Product		Panda Futura Active Size 2	Panda Futura Active Size 2½	Panda Futura Active Size 3	Panda Futura Active Size 4	Panda Futura Active Size 5	Panda Futura Standard Size 1	Panda Futura Standard Size 2	Panda Futura Standard Size 2½	Panda Futura Standard Size 3	Panda Futura Standard Size 4	Panda Futura Standard Size 5	x:panda Size 1S	x:panda Size 1M	x:panda Size 1L	x:panda Size 2S	x:panda Size 2M	x:panda Size 2L	x:panda Size 3S	x:panda Size 3M	x:panda Size 3L	x:panda Size 4S	x:panda Size 4M	x:panda Size 4L	Serval seat Size 1	Serval seat Size 2	Nandu seat Size 1	Nandu seat Size 2	Nandu seat Size 3	Nandu seat Size 4	Stingray seat Size 1	Stingray seat Size 2	
		High-Low Indoor Size 1	Ordinary use	30	50	50	50	-	30	30	50	50	50	-	30*	30*	30*	30*	30*	30*	-	-	-	-	-	-	35	43	50	50	50	50	-
High-Low Outdoor Size 1	Ordinary use	30	50	50	50	-	30	30	50	50	50	-	30*	30*	30*	30*	30*	30*	-	-	-	-	-	-	35	43	-	-	-	-	-	-	
	Transportation in vehicles	-	-	-	-	-	30	30	43	43	43	-	30*	30*	30*	30*	30*	30*	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
High-Low:x Indoor Size 1	Ordinary use	30	50*	50*	50*	-	30*	30*	50*	50*	50*	-	30*	30*	30*	30*	30*	30*	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
High-Low:x Indoor Size 2	Ordinary use	30	50*	50*	50*	43	30*	30*	50*	50*	50*	60	-	-	-	-	-	-	50	50	50	-	-	-	-	-	-	-	-	-	-	-	
High-Low:x Indoor Size 3	Ordinary use	-	-	-	60	85	-	-	-	-	60*	85	-	-	-	-	-	-	60	60	60	80	80	80	-	-	-	-	-	-	-	-	
High-Low:x Outdoor Size 1	Ordinary use	30	50*	50*	50*	-	30*	30*	50*	50*	50*	-	30	30	30	30	30	30	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
	Transportation in vehicles	-	-	-	-	-	30*	30*	43*	43*	43*	-	30	30	30	30	30	30	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
High-Low:x Outdoor Size 2	Ordinary use	30	50*	50*	50*	43	30*	30*	50*	50*	50*	60	-	-	-	-	-	-	50	50	50	-	-	-	-	-	-	-	-	-	-	-	
	Transportation in vehicles	-	-	-	-	43	30*	30*	43*	43*	43*	43	-	-	-	-	-	-	43	43	43	-	-	-	-	-	-	-	-	-	-	-	-
High-Low:v Indoor Size 1	Ordinary use	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	40	-	
High-Low:v Indoor Size 2	Ordinary use	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	40	40	
Nandu Frame Size 1	Ordinary use	30	50*	-	-	-	30*	30*	50*	-	-	-	30*	30*	30*	30*	30*	30*	-	-	-	-	-	-	-	-	50	50	-	-	-	-	
Nandu Frame Size 2	Ordinary use	-	-	50*	60	-	-	-	-	50*	60*	-	-	-	-	30*	30*	30*	60*	60*	60*	-	-	-	-	-	-	-	50	50	-	-	
Combi Frame:x Size 1 20" 12½"	Ordinary use	30	50	50	-	-	30	30	50	50	-	-	30	30	30	30	30	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
	Transportation in vehicles	-	-	-	-	-	30	30	50	50	-	-	30	30	30	30	30	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
Combi Frame:x Size 1 22" 24"	Ordinary use	30	50	50	-	-	30	30	50	50	-	-	30	30	-	30	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
	Transportation in vehicles	-	-	-	-	-	30	30	50	50	-	-	30	30	-	30	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
Combi Frame:x Size 2 20" 22" 24" 12½"	Ordinary use	30	50	50	60	85	30	30	50	50	60	-	30	30	30	30	30	30	60	-	-	-	-	-	-	-	-	-	-	-	-	-	
	Transportation in vehicles	-	-	-	-	-	30	30	50	50	57	-	30	30	30	30	30	30	60	-	-	-	-	-	-	-	-	-	-	-	-	-	-
Combi Frame:x Size 3 20" 12½"	Ordinary use	30	50	50	60	85	30	30	50	50	60	-	30	30	30	30	30	30	60	60	60	-	-	-	-	-	-	-	-	-	-	-	-
	Transportation in vehicles	-	-	-	-	-	30	30	50	50	57	-	30	30	30	30	30	30	60	60	60	-	-	-	-	-	-	-	-	-	-	-	-
Combi Frame:x Size 3 22" 24"	Ordinary use	30	50	50	60	85	30	30	50	50	60	-	30	30	30	30	30	30	60	60	-	-	-	-	-	-	-	-	-	-	-	-	-
	Transportation in vehicles	-	-	-	-	-	30	30	50	50	57	-	30	30	30	30	30	30	57	60	-	-	-	-	-	-	-	-	-	-	-	-	-
Combi Frame:x Size 4 20" 22" 24" 12½"	Ordinary use	30	50	50	60	85	30	30	50	50	60	85	30	30	30	30	30	30	60	60	60	80	80	80	-	-	-	-	-	-	-	-	-
	Transportation in vehicles	-	-	-	-	-	30	30	50	50	57	85	30	30	30	30	30	30	60	60	60	75	75	75	-	-	-	-	-	-	-	-	-
Multi Frame Size 1 - 12½"	Ordinary use	30	50	50	-	-	30	30	50	50	-	-	30	30	30	30	30	30	60	60	-	-	-	-	-	-	-	-	-	-	-	-	-
	Transportation in vehicles	-	-	-	-	-	30	30	50	50	-	-	30	30	30	30	30	30	60	60	-	-	-	-	-	-	-	-	-	-	-	-	-
Multi Frame Size 1 - 22"	Ordinary use	30	50	50	-	-	30	30	50	50	-	-	30	30	-	30	30	30	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
	Transportation in vehicles	-	-	-	-	-	30	30	50	50	-	-	30	30	-	30	30	30	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
Multi Frame Size 2 - 12½"	Ordinary use	30	50	50	60	-	30	30	50	50	60	-	30	30	30	30	30	30	60	60	60	-	-	-	-	-	-	-	-	-	-	-	-
	Transportation in vehicles	-	-	-	-	-	30	30	50	50	57	-	30	30	30	30	30	30	60	60	60	-	-	-	-	-	-	-	-	-	-	-	-
Multi Frame Size 2 - 22"	Ordinary use	30	50	50	60	85	30	30	50	50	60	85	30	30	30	30	30	30	60	60	60	80	80	-	-	-	-	-	-	-	-	-	-
	Transportation in vehicles	-	-	-	-	-	30	30	50	50	57	-	30	30	30	30	30	30	60	60	60	-	-	-	-	-	-	-	-	-	-	-	-
Multi Frame Size 3 - 12½"	Ordinary use	30	50	50	60	85	30	30	50	50	60	85	30	30	30	30	30	30	60	60	60	80	80	-	-	-	-	-	-	-	-	-	-
	Transportation in vehicles	-	-	-	-	-	30	30	50	50	57	85	30	30	30	30	30	30	60	60	60	75	75	-	-	-	-	-	-	-	-	-	-
Multi Frame Size 3 - 22"	Ordinary use	30	50	50	60	85	30	30	50	50	60	85	30	30	30	-	-	-	60	60	-	-	-	-	-	-	-	-	-	-	-	-	
	Transportation in vehicles	-	-	-	-	-	30	30	50	50	57	85	30	30	30	-	-	-	60	60	-	-	-	-	-	-	-	-	-	-	-	-	
Multi Frame:x Size 3 - 12½"	Ordinary use	-	-	-	-	-	-	-	-	-	-	85	-	-	-	-	-	-	-	-	-	80	80	80	-	-	-	-	-	-	-	-	
	Transportation in vehicles	-	-	-	-	-	-	-	-	-	-	85	-	-	-	-	-	-	-	-	-	75	75	75	-	-	-	-	-	-	-	-	
Multi Frame:x Size 3 - 22"	Ordinary use	-	-	-	-	-	-	-	-	-	-	85	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
	Transportation in vehicles	-	-	-	-	-	-	-	-	-	-	85	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
Serval Frame Size 1	Ordinary use	30	35	-	-	-	30	30	50	-	-	-	30	30	-	30	-	-	-	-	-	-	-	-	35	-	-	-	-	-	-	-	
	Transportation in vehicles	-	-	-	-	-	30	30	50	-	-	-	30	30	-	30	-	-	-	-	-	-	-	-	35	-	-	-	-	-	-	-	
Serval Frame Size 2	Ordinary use	30	50	-	-	-	30	30	50	-	-	-	30	30	30	30	30	-	-	-	-	-	-	-	-	50	-	-	-	-	-	-	
	Transportation in vehicles	-	-	-	-	-	30	30	50	-	-	-	30	30	30	30	30	-	-	-	-	-	-	-	-	43	-	-	-	-	-	-	
Stingray Frame	Ordinary use	-	-	-	-	-	30	30	50	-	-	-	30	30	30	30	30	-	-	-	-	-	-	-	-	-	-	-	-	-	40	40	
	Transportation in vehicles	-	-	-	-	-	30	30	50	-	-	-	30	30	30	30	30	-	-	-	-	-	-	-	-	-	-	-	-	-	40	40	
Strong Base	Ordinary use	-	-	-	-	-	-	-	-	-	-	85	-	-	-	-	-	-	-	-	-	80	80	80	-	-	-	-	-	-	-	-	

* Special interface needed